



tesapack[®] 6400

Product Information

Packaging hand dispenser

Product Description

The tesa[®] 6400 hand dispenser is a robust industrial device that applies tesa[®] tapes up to 50 mm width. Its system of a covered blade provides special injury-protection (blade-protection). The tape is cut by pressing the flap on the tape while the serrated cutting blade will “pop out” to cut the tape. The continuously adjustable tension control allows correct dispensing even of easy unwinding tesa[®] tape. tesa[®] 6400 has a soft gummed handle which ensures a comfortable and secure grip.

Application Fields

Place the tesa 6400 dispenser on the carton and pull it towards yourself. The tape is unwound and pressed down by the contact roller. To cut the tape, press the plastic flap on the carton and continue moving the dispenser. Threading: The tesa roll is put on the tape wheel such that the adhesive side of the tape faces the handle. Pull the end of the tape between the tape contact roller and the metal loading gate until the tape is free of wrinkles.

Properties/Performance Values

• Adhesive strength	_NULL	• Roll width max	55 mm
• Applicationfield	Office, Home	• Serrated blade	no
• Batteries included	no	• Solvent free	no
• Batteries required	no	• Spare part service	no
• Low noise unwinding	_NULL	• Suitable surfaces	_NULL
• Material	Metal	• Tear resistance	_NULL
• Max roll length	66 m	• Tension control	yes
• Max. core diameter	3	• Writable	no
• Reusable	yes		

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=06400>