

# 8440 HS

## **Product Information**

Heat activated film for the embedding of chip-modules into smart cards

# **Product Description**

tesa® HAF 8440 is a heat activated, double-sided translucent adhesive film based on thermoplastic copolyamide.

#### **Product Features**

- · Reliable chip module bonding
- Suitable for PVC, ABS and PC cards
- · Good workability on all common implanting lines
- · Good ageing resistance
- · Invisible on assembled card

## **Application Fields**

tesa® HAF 8440 is especially designed for the embedding of chip-modules into smart cards.

- · Suitable for PVC, ABS and PET cards
- Good workability on all common implanting lines
- Good ageing resistance
- Invisible on assembled card

## Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### **Product Construction**

Backing none
Type of liner glassine
Type of adhesive
Total thickness
40 μm

# **Properties/Performance Values**

• Bonding strength 12 N/mm<sup>2</sup>

#### **Additional Information**

**Technical Recommendations:** 

The following values are recommendation for machine parameters to start with. Please note that optimum parameters strongly depend on the type of machine, particular materials for card bodies and chip-modules as well as customer requirements.

1. Pre-lamination:



# 8440 HS

## **Product Information**

#### **Additional Information**

During pre-lamination, the adhesive tape is laminated onto the module belt. This step can be performed inline or offline. The pre-lamination step does not effect the shelf life time of the adhesive tape. Pre-laminated module belts can be stored over the same period of time as the adhesive tape.

## Machine setting:

- Temperature 130 140 °C
- Pressure 4 6 bar
- Time 1.5 3.0 s

#### 2. Module Embedding:

During module embedding, the pre-laminated modules are die cut from the module belt, positioned into the card cavity and permanently bonded to the card body by heat. For this step, the exact handling depends on the type of the implanting line used. Today, two different ways are most common:

Single step process - Machine setting (low temperature):

- Temperature<sup>1</sup> 160 190 °C
- Pressure 65 N/module
- Time 2.0 4.0 s

Single step process - Machine setting (high temperature):

- Temperature<sup>1</sup> 180 210 °C
- Pressure 65 N/module
- Time 1,0 1,5 s

Multiple step process (2 or more heating stamps) - Machine setting:

- Temperature 180 200 °C
- Pressure 65 N/module
- Time (for each step) 0.7 1.2 s

Storage conditions according to tesa® HAF shelf life concept.

Note: Bonding strength values were obtained under standard laboratory conditions (Mean values). Value is guaranteed clearance limit checked with each production batch (Material: Etched aluminium test specimen / Bonding conditions: Temp. = 120 °C; p = 10 bar; t = 8 min)

<sup>&</sup>lt;sup>1</sup> Temperature as measured inside the heating stamp



8440 HS

**Product Information** 

## Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

